Vi2, Vi2Soft & Vi4 Infusion Mesh/Reusable Breather

- These materials are designed for use in vacuum assisted resin infusion processes
- Constructed from HDPE, Vi2 and Vi4 are manufactured in a diamond mesh pattern, to allow controlled resin flow across the laminate
- Allows for a sustainable air evacuation route, when in contact with appropriate bagging materials
- The product may also prove beneficial in debulking applications as it can be utilised
 as a reusable breather beneath bagging film, to ensure adequate air flow to vacuum
 breach units

PHYSICAL PROPERTIES

Maximum Use Temperature 80°C Green

AVAILABILITY & PACKAGING

Standard roll sizes
 Vi2 - 25m x 1.20m wide
 Vi4 - 25m x 1.25m wide
 Vi2soft - 50m x 1.2m wide

STORAGE & HANDLING

No special requirements

Aerovac Systems Ltd.

Tel: 01274 550500 Fax: 01274 550501 e-mail: sales@aerovac.com website: www.aerovac.com

All statements, technical information and recommendations contained in this publication are based on tests believed to be reliable, but their accuracy and/or completeness are not guaranteed. The user shall determine the suitability for this particular purpose and shall assume all risk and liability in connection herewith.